

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2019

© COPYRIGHT 1999

TE Connectivity. All Rights Reserved. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER EO PI7504	10DEC2001	ST	RDR
C		REVISED PER EO P20851	25MAR2011	ST	RDR
C1		REVISED PER PCN E-19-016328	18OCT2019	JA	IG
C2		REVISED PER PCN E-21-001566	11FEB2021	MK	IG

3D VIEW

2. ALL PART NUMBERS ARE IN ACCORDANCE WITH RoHS STANDARDS.

PART INFORMATION:

PART NUMBER	MATERIAL	HOLE DIAMETER
1027-001-0800	STAINLESS STEEL	.433 [11.0]
1027-002-0800	STEEL-ZINC PLATE	.512 [13.0]
1027-006-0800	STAINLESS STEEL	.512 [13.0]
1027-014-0800	STEEL-ZINC PLATE	.323 [8.2]

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
INCHES [mm]

MATERIAL

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±.025 [0.64]
4 PLC	±
ANGLES	±0° 30' 0"

FINISH

DWN 09NOV1999

S.THEIS

CHK 23MAR2011

B.BYFORD

APVD 15MAR2011

S.BEARD

PRODUCT SPEC

APPLICATION SPEC

114-151009

WEIGHT

10.5g

CUSTOMER DRAWING

NAME

METAL CLIP / MOUNTING BRACKET  
FOR 8 WAY RECEPTACLE  
DT SERIES

SIZE

A3

CAGE CODE

4AFU8

DRAWING NO

1027-001/002-006-014-0800

RESTRICTED TO

-

SCALE

3:1

SHEET

1 OF 1

REV

C2

TE INTERNAL PN	DEUTSCH PN
1027-001-0800	1027-001-0800
1027-002-0800	1027-002-0800
1027-006-0800	1027-006-0800
1027-014-0800	1027-014-0800

TE Connectivity

1470-19 (3/11)