




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E2	REVISED	ECR-23-185274	13SEP2023	AG RK



1. MUST BE KEPT BETWEEN **-A-** AND 2
2. TO BE MATED WITH PLUG HOUSING SMOOTHLY
3. APPLIED TAB CONTACT; P/N 173633 AND 173645
4. APPLIED PLUG HOUSING; P/N 173851
5. PRODUCT SPEC; 108-5264

1. **-A-** 面より 2mm の範囲で測定
2. 相手ハウジングと所定の機能を満足して嵌合できること
3. 内装するタブコンタクトは型番 173633、173645
4. 嵌合相手ハウジング型番 173851
5. 製品規格：108-5264



OBSOLETE	V-2	白 (WHITE)	1-174933-1
		オレンジ (ORANGE)	174933-8
OBSOLETE	HB	濃灰 (DARK GRAY)	174933-6
		青 (BLUE)	174933-5
		緑 (GREEN)	174933-4
		黒 (BLACK)	174933-2
		白 (WHITE)	174933-1
		使用材料難燃グレード (FLAMMABILITY OF MATERIAL)	色 (COLOR)
			型番 (PART NUMBER)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	S.FUJITA	05DEC08
CHK	K.BETSUI	05DEC08
APVD	K.BETSUI	05DEC08
PRODUCT SPEC	108-5264	
APPLICATION SPEC	-	
WEIGHT	0.000000	A3 00779 C-174933
CUSTOMER DRAWING		SCALE 2:1 SHEET 1 OF 1 REV E2

STE TE Connectivity

070 SERIES MULTILOCK CONNECTOR
12 POSITION CAP HOUSING WIRE TO WIRE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

一般公差

10 \geq	: ±0.2
30 \geq	> 10 : ±0.25
	> 30 : ±0.3
ANGLE	: ±3°

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH
PBT	-