





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B1		REVISED PER ECO-20-017180	07DEC2020	RZ	RS

- FOR USE IN PANELS UP TO 6.35 [.250] MAXIMUM THICK.
- ITEM 2 AND ITEM 3 WILL BE UNASSEMBLED AND PACKAGED SEPARATELY.

-  CENTER CONTACT PLATING THICKNESS GOLD 27u" ~ 33u"
-  CENTER CONTACT PLATING THICKNESS GOLD 5u" ~ 8u"



SUGGESTED PANEL CUTOUT
SCALE 8:1

9-414815-1	1-329492-1	227529-4 	5227726-5
9-414815-1	1-329492-1	227529-3 	5227726-3
9-414815-1	1-329492-1	227529-2	5227726-2
9-414815-1	1-329492-1	227529-1	5227726-1

 JAM NUT QTY=1	 LOCKWASHER QTY=1	 JACK ASSY QTY=1	PART NUMBER
--	---	--	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - DOCK5 21APR2005	TE Connectivity	
DIMENSIONS: INCHES		CHK J. HAVENER 21APR2005	NAME SOLDER JACK, ISOLATED, 50 OHM, BNC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. LIPPERT 21APR2005	DRAWING NO C=5227726	
0 PLC ± -		PRODUCT SPEC	SIZE A2	CAGE CODE 00779
1 PLC ± -		APPLICATION SPEC	DRAWING NO C=5227726	RESTRICTED TO
2 PLC ± -			SCALE 8:1	SHEET 1 OF 1
3 PLC ± -			REV B1	
4 PLC ± -				
ANGLES ± -				
MATERIAL	FINISH	WEIGHT 0.000000	CUSTOMER DRAWING	