

4

3

2

1

© 2020 TE Connectivity. All Rights Reserved.

REVISIONS

1. MAT'L THICKNESS 1.778±0.051 [.070±.002]

2. NOTE DELETED.

3 STAMP: AMP 2W\*60-75 APPROX AS SHOWN

4 MATERIAL: COPPER PER ASTM B152.

5 FINISH: TIN PLATE 0.00254 [.000100] MIN  
EXT THICKNESS PER ASTM B545.

BRAZED SEAM

9.398 [.370]  
MIN

SCALE 1:1

50	LOOSE PIECE	132101-2
QTY	PACKAGE TYPE	PART NUMBER

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F]
VOLTAGE RATING: N/A
CIRCULAR MIL AREA: 26.7-42.2 mm <sup>2</sup> [52,600-83,700] SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm/ INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ±-
	2 PLC ±
	3 PLC ±0.127 [.005]
	4 PLC ±-
	ANGLES ±3
MATERIAL	FINISH
4	5

DWN JJ. DESPRETZ 04JUL2005
CHK G-ROBERT 04JUL2005
APVD Y-PETRONIN 04JUL2005
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

TE Connectivity		NAME TERMINAL, RING TONGUE, SOLISTRAND WIRE SIZE: 2 AWG,	
		SIZE A3	CAGE CODE -
DRAWING NO C-132101		RESTRICTED TO	
SCALE 2:1		SHEET 1 OF 1	REV A3

1470-19 (3/13)