


寸法公差は ±0.20
(TOLERANCE : ±0.2)
パネル取付穴
(DIMENSION OF PANEL)



キャビティマーク
(CAVITY MARK)

NOTES:

1. APPLIED CONTACT P/N : 170359, 170360, 170361, 170362.
2. MATING CONN ; PLUG HOUSING P/N 172338.
- ③ PANEL THICKNESS ; 0.8~2.0 mm
4. PRESS DIRECTION OF PANEL MUST BE SAME AS HOUSING INSERTED DIRECTION.
5. INSTRUCTION SHEET ; IS-105J
6. PRODUCT SPEC : 108-5151.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

注:

1. 使用端子型番は 170359, 170360, 170361, 170362
2. 嵌合相手ハウジング型番は 172338
- ③ 適用パネル厚 0.8~2.0 mm.
4. 取付穴打抜方向とハウジングの挿入方向は同じである。
5. 取扱説明書 : IS-105J
6. 通用製品仕様書: 108-5151

OBSOLETE

黄 (YELLOW)	1- 172330 -4
黒 (BLACK)	1- -9
青 (BLUE)	1- -6
緑 (GREEN)	1- -5
赤 (RED)	1- -2
自然色 (NATURAL)	172330 -1
色 (COLOR)	型番 (P/N)

材料 (MATERIAL) 6/6 ナイロン (UL94V-2) (NYLON 6/6 UL94V-2)	一般公差 TOLERANCE ±0.3 EXCEPT ±1° AS NOTED	TE TE Connectivity	
仕上 (FINISH) 色: 表参照 HOUSING COLOR : SEE TABLE	DR. <i>R. Yuasa 4/20 21</i> CHK. <i>St. Tompa 4/21 21</i> DE. <i>St. Tompa 4/21 21</i> APP.	名称 (NAME) MINI-UNIVERSAL MATE-N-LOK CONN. CAP HOUSING 4 Pos. (UL94V-2) 4極ミニユニバーサルメイトンロックコネクタ キャブ7°ハウジング (UL94V-2)	
		SIZE B	LOC J
		番号 (NO.) C-172330	
		尺度 (SCALE) 2:1	REV. A4
		SHEET —	

PRINT DIST 単位: 概 DIMENSIONS IN MM DO NOT SCALE PRINT

A4	REVISED PER ECR-16-010553	BW	SG	03AUG2017
LTR.	変更 (REVISION RECORD)	DR.	CHK.	DATE