


NUMBER C-174453

METRIC

PRINT DIST

単位: 概寸法 (3rd ANGLE PROJECTION)

PRINT DIST




注:

1. 適用電線範囲 : AWG #28-26 (UL1571, UL1061)  
被覆外径 : 0.83-0.97  
(但し、使用電線について適合性に確認が必要です。)
2. 材料 : ハウジング : ガラス入りP.B.T UL94V-0  
コンタクト : 銅合金
3. 適用製品規格番号 : 108-5217
4. 取付適用規格番号 : 114-5103

NOTES:

1. APPLICABLE WIRE SIZE : AWG #28-26 (UL1571, UL1061)  
INSULATION DIA RANGE : 0.83-0.97
2. MATERIAL :  
HOUSING : P.B.T. (G.F)UL94V-0  
CONTACT : COPPER ALLOY
3. PRODUCT SPEC : 108-5217
4. APPLICATION SPEC : 114-5103

1-174453-5	15	28	32
1- ↑ -4	14	26	30
1- -3	13	24	28
1- -2	12	22	26
1- -1	11	20	24
1- -0	10	18	22
	-9	9	16
	-8	8	14
	-7	7	12
	-6	6	10
	-5	5	8
	-4	4	6
	-3	3	AS SHOWN 図示
174453-2	2	AS SHOWN 図示	
LIGHT BLUE ライトブルー	Pos 極数	G	H
PART No. 製品型番			



RECOMMENDABLE P.C. BOARD LAYOUT  
推奨基板寸法  
(適用基板厚0.8~1.6)  
(P.C.B THK: 0.8~1.6)

C2	REVISED PER ECN-21-132655	R.S	M.S	28DEC21
C1	REVISED PER ECN-21-131030	R.S	M.S	16DEC21
C	REVISED ECR-07-000873	C.Z	S.Y	18JAN 07
B	REDRAWN (FJ00-1083-99)	J. T		25 AUG 99
LTR	変更 (REVISION RECORD)	DR	CHK	DATE

Copyright ©1999 AMP (Japan), LTD. ALL RIGHTS RESERVED.	Copyright ©1999 AMP (Japan), LTD. ALL RIGHTS RESERVED.
包含電線断面 (WIRE RANGE)	被覆外径 (INSULATION DIA.)
NOTE 1 mm <sup>2</sup> (AWG - )	NOTE 1 mmφ
材料 (MATERIAL)	仕上 (FINISH)
NOTE 2	
DR. 23/AUG/99 J. TSUJI	DE. 23/AUG/99
CHK 25/AUG/99 T. Taniguchi	APP. 23/AUG/99 S. Yamada

AMP		株式会社 川崎	
Kawasaki, Japan			
名称 (NAME)	CT AMP-IN HEADER 2mm PITCH MT HORIZONTAL (H-TYPE)		
一般公差 (GENERAL TOLERANCE)	SIZE	LOC	番号 (No.)
10以下 : ±0.2 10~30以下 : ±0.25 30~100以下 : ±0.3 角 度 : ±3°	C	J	C-174453
尺度 (SCALE)	REV.	SHEET	
5-1	C2	1 OF 1	