


RAYCHEM

THERMOFIT MOULDED PARTS

SPECIFICATION CONTROL DRAWING



Potting Ports Are Optional
When Specified They Will Be Located As Shown

TABLE OF DIMENSIONS


a - As Supplied; b - After unrestricted recovery

PART NUMBER	H		J		P		R		W		DRN	PART DESCRIPTION		PART No.	REV.
	Min a	Max b	Min a	Max b	±10% a	±10% b	±10% a	±10% b	±20% a	±20% b		CKD	SDS		
232W012-	24,0	20,0	24,0	5,0	-	25	-	28,4	-	1,5			S-B00T	232W012-	A
232W012-	.95	.79	.95	.20	-	.98	-	1.12	-	.06					

Note: Drawing shows typical part after unrestricted recovery, unless otherwise specified.
Metric Dimensions
Imperial Dimensions
© RAYCHEM LIMITED

FEB. 1976

(Ordering Information)



(COMPATIBILITY CHART)

MATERIAL DASH NUMBER	MATERIAL DESCRIPTION	COATING SLASH NUMBER
-3	POLYOLEFIN, SEMI-RIGID	/42, /86
-4	POLYOLEFIN, FLEXIBLE	/42, /86
-25	ELASTOMER, FLUID RESISTANT	/86, /225

AS SUPPLIED DIMENSIONS ARE FOR UNCOATED PARTS,
WHEN COATING IS ADDED, ENTRY DIAMETERS WILL REDUCE BY 1.5mm MAX.

POTTING PORTS ARE OPTIONAL
WHEN SPECIFIED BY SUFFIX "-00"
THEY WILL BE LOCATED AS SHOWN

Raychem
Electronics OEM Division Europe
Swindon, Wiltshire, England.
Telephone: (01793) 528171 Fax: 573923