


SCALA NON IMPEGNATIVA  
(DO NOT SCALE)  
DIMENSIONI IN mm  
DIMENSIONS IN

**METRIC**

PROIEZIONE EUROPEA  
(EUROPEAN PROJECTION)



STAGNATO	OTTONE	281623-2
FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)

**CUSTOMER DWG. FOR REFERENCE ONLY**      **DISEGNO PER CLIENTE SOLO PER RIFERIMENTO**

THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION 19	
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA ALL INTERNATIONAL RIGHT RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING			
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)	SCALA (SCALE)
± 0.4	3,0 mm DIA. Max	0,3 ~ 1,0 mm <sup>2</sup>	#
ANGOLI (ANGLES) ± 2°	<b>AMP</b> AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)		

DIS. (DR.) *[Signature]* 20-4-84      DESCRIZIONE (DESCRIPTION) **MAG MATE POKE-IN**  
 0,3 ~ 1,0 mm<sup>2</sup> (STD. VERSION)

CONT. (CHK) <i>[Signature]</i> 26-4-84	LOC. SIZE	NUMERO (DWG NO)	REV.	FOGLIO (SHEET)
	IA4	C-281623	A	1 DI 1 (OF)

DISTRIBUZIONE (PRINT DIST.)	A	In Produzione	CB	4-Feb-87
	REV.	REVISIONI (REVISION RECORD)	DIS. (DR)	DATA (DATE)