


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14	F	REDRAWN PER 0720-0377-94	25OCT94	LO ME

△ STAMP AMP 16-14* APPROX AS SHOWN



- 2. WIRE INSUL DIA, 3.05-4.32 [0.120-.170]
- 3. TONGUE MATL THK, 0.79±0.05 [0.031±.002]

1000	LOOSE PIECE	322825
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 343°C [650°F]	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN L OLMEDA 25OCT94	AMP Incorporated Harrisburg, PA 17105-3608
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [in]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M ELLIS 25OCT94	
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: -		0 PLC ±-	NAME WIRE SPLICE, STRATOTHERM DIAMOND GRIP, WIRE SIZE, 16-14 AWG	
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: 1.04mm² - 2.62mm² [2050-5180]		1 PLC ±-		2 PLC ±0.20 [0.008]
		STRANDED WIRE	MATERIAL BODY, CU PER ASTM B152	3 PLC ±-	APVD S BORTNER 25OCT94	SIZE A3
			SLEEVE, NI SIL PER ASTM B122	4 PLC ±-	PRODUCT SPEC -	CAGE CODE 00779
				FINISH BODY, NP, QQ-N-290	APPLICATION SPEC -	DRAWING NO C-322825
				ANGLES ±-	WEIGHT -	SCALE 6:1
					CUSTOMER DRAWING	SHEET 1 OF 1
						REV F