


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECO-17-014338	17MAY2018	RS	DR



- FOR 2.032-3.048[.080-.120] WIRE INS DIA
- MATERIAL:
SPLICE - COPPER PER ASTM B152
- FINISH:
SPLICE - TIN PER ASTM B545
INSULATION:
COLOR - TRANSLUCENT RED LETTERING



THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. © COPYRIGHT - TE Connectivity Ltd.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
TOOLING INFORMATION	1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]
VOLTAGE RATING: 600V (1000 V SIGNS OR FIXTURES)
WIRE CROSS SECTIONAL AREA RANGE, 1.04-2.62mm ² [2,050-5180] CIR MILS SOLID OR STRANDED

1000	LOOSE PIECE	324138
QTY	PACKAGE TYPE	PART NO.

DIMENSIONS: mm [INCHES]	DWN RAVI S 17MAY2018	MATERIAL -	FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 5°	CHK ROHDE DANIEL F 17MAY2018	TE Connectivity Ltd.	
	APVD ROHDE DANIEL F 17MAY2018		
	PRODUCT SPEC UL 486 A-B	NAME WIRE SPLICE	
APPLICATION SPEC 114-2161	PLASTI-GRIP - BUTT, WIRE SIZE: 22-16 AWG		RESTRICTED TO -
WEIGHT	SIZE A4	CAGE CODE 00779	DRAWING NO C-324138
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
		REV G1	