


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION - , - .  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
		F		REVISED PER ECO-14-019230	04APR2015	NK	DR

**AMP**  
WIRE RANGE

---

2 AWG  
STRANDED



1 WIRE INSULATION DIA 11.30 [.445] MAX.

**OBSOLETE**

50	LOOSE PC	324623
QTY	PACKAGE TYPE	PART NO

<b>AMP INCORPORATED CUSTOMER SERVICE SYSTEMS</b>	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 105° C
VOLTAGE RATING: 600 V MAX
CIRCULAR MIL AREA: 26.65-45.41mm <sup>2</sup> [52,600-83,700] STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± -
MATERIAL COPPER PER ASTM B-152 NYLON, COLOR:RED	FINISH TIN PLATE PER MIL-T-10727

DWN	8-27-93
S.S. GOULDEN	
CHK	8-27-93
R. HERSEY	
APVD	8-27-93
B. BARE	
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	-
CUSTOMER DRAWING	

<b>STE</b> TE Connectivity			
NAME SPLICE, BUTT, SINGLE TO SINGLE, TERMINYL, WIRE SIZE: 2 AWG			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-324623	-
SCALE	NTS	SHEET	1 of 1
REV	F		