


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .19 .  
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16		D	REV PER EC 0A40-0247-02	10JUL02	JWD	JD

1. DIMENSIONS IN [ ] ARE IN INCHES.
2. 0.5dB MAX INSERTION LOSS.
3. 55dB MIN RETURN LOSS.



15±0.15	[591±6]	1-492194-5
10±0.15	[394±6]	1-492194-0
2.5±0.05	[98.4±2.0]	492194-6
5±0.08	[197±3]	492194-5
1.5±0.05	[59.1±2.0]	492194-4
3±0.05	[118±2]	492194-3
2±0.05	[79±2]	492194-2
1±0.05	[39±2]	492194-1
L		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.BAUBLITZ 09NOV98	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: METERS ■ [INCHES]		CHK N.MILLER 10DEC96		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD N.MILLER 10DEC96	NAME PIGTAIL CABLE ASSEMBLY, SINGLEMODE LDS, FC/UPC	
MATERIAL - FINISH -		PRODUCT SPEC -	APPLICATION SPEC -	RESTRICTED TO -
		WEIGHT -	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-492194	SCALE NTS
			SHEET 1	OF 1
			REV D	