





P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECO-20-000700	12JUN2020	SH	SH



- ① MATERIAL: HOUSING: GLASS FILLED 66NYLON (UL94V-0) BLACK  
CONTACT: PHOSPHOR-BRONZE
- ② FINISH: CONTACT: 0.0003 MIN. Au AT CONTACT AREA,  
0.001MIN. TIN AT TINE, OVER Ni
- ③ BOSS FOR POSITIONING: P/N -1, -2, -3, -4
- ④ OBSOLETE



180	39	49.53	49	62.23	—	115.57	51.53	64.23	117.57	120.66	128.19	125.54	④ ③ ① 8
140	29	36.83	39	49.53	—	90.17	38.83	51.53	92.17	95.26	102.79	100.14	-6
100	—	—	—	—	49	62.23	—	—	64.23	67.32	74.85	72.2	-4
80	—	—	—	—	39	49.53	—	—	51.53	54.62	62.15	59.5	-3
60	—	—	—	—	29	36.83	—	—	38.83	41.92	49.45	46.8	2
40	—	—	—	—	19	24.13	—	—	26.13	29.22	36.75	34.1	5176375-1
POS.	a	A	b	B	c	C	D	E	F	G	H	J	P/N

P.C. BOARD LAYOUT  
(CONNECTOR MOUNT SIDE)

LEAD FREE

GENERAL TOLERANCE  
10 ≥ : ±0.2  
30 ≥ > 10: ±0.25  
100 ≥ > 30: ±0.3  
ANGLES: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 概 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
0 PLC ±-	1 PLC ±-
2 PLC ±-	3 PLC ±-
4 PLC ±-	ANGLES ±-
MATERIAL 材料	FINISH 仕上
①	②

DWN	ROY HAO	31AUG04
CHK	STEVEN YAO	31AUG04
APVD	I. ENOMOTO	31AUG04
PRODUCT SPEC	製品規格	
APPLICATION SPEC	取付適用規格	
WEIGHT	0.000000	

**STE** TE Connectivity

AMP FH CONNECTOR RECEPTACLE (VERTICAL)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-5176375	—

SCALE 2:1 SHEET 1 OF 1 REV B