

4

3


2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CE	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED PER NPR	22MAR06	CSV	JD

1. DIMENSIONS IN [] ARE IN INCHES
2. 0.5dB MAX INSERTION LOSS
3. 55dB MIN RETURN LOSS
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



15±0.15 [591±6]	1-5492194-5
10±0.15 [394±6]	1-5492194-0
2.5±0.05 [98.4±2.0]	5492194-6
5±0.08 [197±3]	5492194-5
1.5±0.05 [59.1±2.0]	5492194-4
3±0.05 [118±2]	5492194-3
2±0.05 [79±2]	5492194-2
1±0.05 [39±2]	5492194-1
L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.S.VASU 22 MAR 06	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN 22 MAR 06		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.DUNCAN 22 MAR 06	NAME PIGTAIL CABLE ASSEMBLY, SINGLEMODE LDS, FC/UPC	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	APPLICATION SPEC -	
MATERIAL -	FINISH -	WEIGHT -	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING			DRAWING NO C-5492194	RESTRICTED TO -
			SCALE NTS	SHEET 1 OF 1
			REV A	