





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION DEC, 2004.  
 © COPYRIGHT 2004 By - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A1	RELEASED PER ECO-19-008592	23MAY2019	R.L H.L



OBSOLETE

WELDING THE COVER TAPE AROUND THE OUTER PERIPHERY  
 カバーテープを外周部へ溶着  
 剥離角度、165°~180° PEELING ANGLE.




INSTRUCTION SHEET		DIMENSIONS		数量 (ヶ)		植数		リール巻 コネクタ型番 TAPING P/N	
取扱い説明書	411-5654	W <sub>2</sub>	W <sub>1</sub>	D	C	B	A	数量 (ヶ)	植数
22.4	16.4	9.3	16	---	7.5	900	12	1-6376826-2	
29.5	25.5	16.5	24	---	11.5	900	30	3-6376826-0	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	DWN M.IWASAKI 27DEC04	<b>TE</b> TE Connectivity Ltd.
0 PLC ± 0.2	1 PLC ± 0.2	CHK Y.NAKAZAWA 27DEC04	
2 PLC ± 0.2	3 PLC ± 0.2	APVD T.KUSUHARA 27DEC04	NAME 名称
4 PLC ANGLES ± 0.2 寸		PRODUCT SPEC 製品規格 108-5424	0.8mm PITCH FINE STACK CONNECTOR MATING HEIGHT 4.2mm
MATERIAL 材料	FINISH 仕上	APPLICATION SPEC 取付適用規格	SIZE A3 CAGE CODE 00779 DRAWING NO. 番号 G=6376826
		WEIGHT	RESTRICTED TO
		CUSTOMER DRAWING	SCALE 尺度 4:1 SHEET 1 OF 3 REV A1

REVISIONS					
変更					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

本図：コネクタ図  
AS SHOWN: CONNECTOR DWG



OBSOLETE

△ 材料：ハウジング - 6T NYLON (高耐熱性ナイロン)  
 ガラス30%, 色：ベージュ  
 コンタクト - 燐青銅・錫めっき (0.2t)  
 テール プレート - 燐青銅・錫めっき (0.2t)

△ MATERIAL: HOUSING - 6T NYLON (HIGH HEAT-RESISTED NYLON), GF30%,  
 COLOR: BEIGE.  
 CONTACT - POST-TIN/PHOS-BROZ (0.2t)  
 TAIL PLATE - POST-TIN/PHOS-BROZ (0.2t)

-	8	9	5.6	4	12	1-6376826-2
OBSOLETE	0.49	15.2	16.2	12.8	11.2	3-6376826-0
	重量 (g) WEIGHT	H	G	F	E	極数 POS.
						型番 PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity Ltd.	
DIMENSIONS: 単位: 耗 mm		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD			
0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES ± 3°		PRODUCT SPEC 製品規格 108-5424 APPLICATION SPEC 取付適用規格			
MATERIAL 材料		WEIGHT		NAME 名称 エンボス詰 キャップ・アッセンブリ (ボス付) ON TAPING EMBOSS CAP ASSEMBLY WITH BOSS 0.8mm PITCH FINE STACK CONNECTOR MATING HEIGHT 4.2mm	
△		CUSTOMER DRAWING		SIZE A3 CAGE CODE 00779 DRAWING NO. 番号 G=6376826 RESTRICTED TO	
		SCALE 尺度 10:1		SHEET 2 of 3 REV A1	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

DEC ,2004.

© COPYRIGHT 2004 By -


ALL RIGHTS RESERVED.

REVISIONS

変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

0.8mm PITCH FINE STACK CONNECTOR  
(MATING HEIGHT 4.2mm)



**OBSELETE**

嵌合状態図

PLUG ASSY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

製品規格  
108-5424

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

NAME  
名称

エンボス詰 キャップ・アッセンブリ (ボス付)

0.8mm PITCH FINE STACK CONNECTOR  
MATING HEIGHT 4.2mm

SIZE

CAGE CODE

DRAWING NO

番号

A3

00779

G=6376826

RESTRICTED TO

DIMENSIONS:  
単位: 概  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:  
一般公差



- 0 PLC ± 0.2
- 1 PLC ± 0.2
- 2 PLC ± 0.2
- 3 PLC ± 0.2
- 4 PLC ± 0.2
- ANGLES ± 3'

MATERIAL  
材料

FINISH  
仕上

SCALE  
尺度 NTS

SHEET  
3 OF 3

REV  
A1