



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.


REVISIONS					
P	LTN	DESCRIPTION	DATE	DWN	APVD
C1		ADDED ALUMINIUM WIRE RANGE	08NOV19	MB	PKS

1  SLOT TERMINATES EITHER SINGLE OR DOUBLE MAGNET WIRE OF THE SAME SIZE.  
 COPPER RANGE 0.36-0.51mm [#27-#24] AWG  
 ALUMINIUM RANGE 0.45-0.51mm [#25-#24] AWG  
 ALUMINIUM WIRE RANGE APPLIES FOR POST TIN PLATED PARTS ONLY.

2 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 8.38±0.08 [.330±.003] CENTERS.



63808-1  
 PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: MICHAEL S. FEHNER 19/SEP/94	 TE Connectivity	
		CHK: JEFF R. RUTH 21/SEP/94		
DIMENSIONS: in mm [INCHES]		APVD: NELSON E. NEFF 21/SEP/94 PRODUCT SPEC: 108-2012 APPLICATION SPEC: 114-2046		NAME: TERMINAL, TAB, 3.18 [.125], MAG-MATE
MATERIAL: #4M PRE-MILLED BRASS FINISH: TIN PLATE		WEIGHT: 0 CUSTOMER DRAWING		SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=63808 RESTRICTED TO: -
1471-9 (1/15)		SCALE: 8:1		SHEET: 1 of 1

63808

A