


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M	REVISED PER ECR-24-208943	17MAY2024	DK	JP

- 1. 150°C TEMPERATURE RATING FOR THIS HOUSING IS FOR SHORT TERM DURATION ONLY. MAXIMUM OPERATING TEMPERATURE REMAINS 105°C.
- 2. INDIVIDUAL CORING FEATURES AROUND BASES OF SILOS MAY NOT BE PRESENT IN ALL LOCATIONS SHOWN.



1	HIGH TEMP NYLON, UL94V-2, BLACK	1-770581-0
	NYLON, UL94V-0, WHITE	770581-1
	MATERIAL	PART NO

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 12-MAY-2004	TE TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK C. JONES 12-MAY-2004		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 12-MAY-2004	NAME PLUG, 12 CIRCUIT, MINI UNIVERSAL MATE-N-LOK™	
0 PLC ±		PRODUCT SPEC	SIZE A2	
1 PLC ±		APPLICATION SPEC	CAGE CODE 00779	DRAWING NO C=770581
2 PLC ±			RESTRICTED TO	
3 PLC ± 0.13 [.005]			SCALE 5:1	
4 PLC ±			SHEET 1 of 1	
ANGLES ±			REV M	
FINISH		WEIGHT 0.000000		
MATERIAL		CUSTOMER DRAWING		