



3-DIMENSIONAL MODEL NTS

- UNIT ACCEPTS 1.14 [.045] SQUARE OR ROUND POST.
- UNIT ACCEPTS STANDARD SL-156 CONTACTS.
- UNIT ACCEPTS KEYING PLUG 640254-1 AND KEYING PIN 640255-1.
- CIRCUIT I.D. NUMBER(S), TO BE LOCATED SEQUENTIALLY AS SHOWN.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- OPTIONAL CONSTRUCTION (BOTH CORNERS) UP TO 1.27 [.050].
- REFERENCE: THIS PART IS THE SAME AS 640250-8, EXCEPT FOR OPTIONAL CIRCUIT I.D. MARKING IS NOT ALLOWED.

31.65	[1.246]	8	770696-8
A ±0.25	[.010]	NO. OF CIRCUITS	PART NO

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DIN		REVISIONS			
mm	[INCHES]	0 PLC	±	7-31-92	TE Connectivity				
1 PLC	±	1 PLC	±	7-31-92 <td colspan="3" rowspan="4"> <b>STE</b> TE Connectivity                  HOUSING WITH LOCKING RAMP, SL-156             </td>	<b>STE</b> TE Connectivity HOUSING WITH LOCKING RAMP, SL-156				
2 PLC	±	2 PLC	±	9-28-92					
3 PLC	±	3 PLC	±						
4 PLC	±	4 PLC	±						
ANGLES	±	ANGLES	±		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
					WEIGHT				
MATERIAL: NYLON, UL 94V-0				FINISH: -				CUSTOMER DRAWING	