



LOC		DIST		P		F		ZONE		LTR		REVISIONS			
AG	53											DESCRIPTION	DATE	APPD	
												D	REVISED PER AG-3456	11-11-93	RT



- ① MATERIAL SHALL BE POLYPHENYLENE SULFIDE.
- ② PAD AREA TO HAVE NO MATTE FINISH AND IS THERE ONLY TO INDICATE THE LOCATION OF EXTRACTION TOOL SLOTS.

SECTION Z-Z

PIN NO. 1 IDENTIFIER

PIN NO. 1 IDENTIFIER
 (ALTERNATE LOCATION)

②
 4 PLC

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± 0.13 [.005] ANGLES ± -		DR 6-13-88 R.W.BROWN	AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME COVER, MICRO-PITCH SOCKET, 132 POSITION		
MATERIAL ①		CHK 6-13-88 K.WALKER			
FINISH NATURAL		PRODUCT SPEC -	APPLICATION SPEC -	SIZE D	CAGE CODE 00779
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		WEIGHT -	SCALE 10:1	DRAWING NO C-821942	SHEET 1 OF 1

CUSTOMER DRAWING