



C 880 191

DO NOT SCALE
DIMENSIONS IN


METRIC



3.0 14.5




22.9



R 1.5

16.4



3.5



1.0

ZBC 953 637	NATURAL	NYLON 6.6	880 191 - 1
VW PART NUMBER	FINISH	MATERIAL	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY		THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 19	
		© COPYRIGHT 19 83 BY AMP DO BRASIL LTDA S.P. ALL INTERNATIONAL RIGHTS RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.	
TOLERANCES UNLESS OTHERWISE STATED		IMS. DIA. RANGE	WIRE RANGE
DEC. ± 0,5		— // —	— // —
ANGLES ± 1°		SCALE	
		— // —	
DR. <i>[Signature]</i>		AMP AMP do BRASIL LTDA	
CHK. <i>[Signature]</i> 17/11/83		São Paulo, Brasil	
D	VW. PNO. MODIFICADO	G.F.M. <i>[Signature]</i>	30.11.83
C	VW. PNO. MODIFICADO	G.F.M. T.V.	26.10.83
B	ERA P79-29143	G.F.M. T.V.	2.8.83
A	REDES. C/ MODIF.	G.F.M. T.V.	17.5.83
REVISION	RECORD	DR	CHK
DATE	APP.	DESCRIPTION	
		5 WAY .250 & .110 COMB. FASTIN-ON RECEPT. HS6.	
		DWG NO	SHEET
		A3 C 880 191	1 of 1