
	SPECIFICATION CONTROL DRAWING	(CXA-0170
TITLE	POWER CABLE	Date 7-2-07	Revision C



CONSTRUCTION DETAILS									
	BRAIDED		TARGET	FINISHED WIRE					
PART NUMBER 1/	COPPER CONDUCTOR (AWG EQUIV.)	CONDUCTOR STRANDING (number x AWG)	CONDUCTOR DIAMETER (in.)	NOMINAL RESISTANCE AT 20°C (ohms/1000 ft.)	NOMINAL DIAMETER (in.)	NOMINAL WEIGHT (lbs/1000 ft.)			
CXA-0170-0000-0	0000	2304 x 30	1.25 x 0.40	.056	1.340 x 0.490	951.			

WIRE RATINGS AND ADDITIONAL REQUIREMENTS

VOLTAGE RATING: 600 volts (rms) at sea level INSULATION ELONGATION AND TENSILE STRENGTH: Elongation 150% (minimum)
Tensile Strength, 2000 lbf/in² (minimum)

Outer jacket color will be black (designated by a "-0" appended to the part number, e.g. CXA-0170-0000-0).

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.							
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902" MAY BE REPLACED BY "AXXX".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.							
Page 1 of 1	RAYCHEM and THERMORAD are trademarks of Tyco Electronics Corporation.		Raychem Wire & Cable				
	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL	Redwood City, 0	501 Oakside Avenue Redwood City, CA 94063-3800				
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.	Electronics	Phone: 1-800-227-8816 Fax: 1-650-361-6297				