





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION . 1995
 (C) COPYRIGHT 1995 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD	変更	
0		作図 (DRAWN)	FJ00-3206-95	31Oct95	E.T	I.H		
A		変更 (REVISED)	ECR-08-027468	29OCT08	M.S	S.M		
A1		REVISED	ECR-23-178596	19JUNE23	AK	JP		



NOTE:

- INSULATION DIA RANGE $\phi 6.0 \sim \phi 7.5$
- SCREWS; CROSS-RECESSED HEAD MACHINE SCREWS M2.6 L10
- NUTS; HEXAGON NUTS M2.6
- MATING HOUSING □-172169-□

- | : 本図
 (- | : AS SHOWN)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE, AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN E. TAKEMASA 4/SEP/95 CHK I. HASEGAWA 31Oct95 APVD I. Hasegawa 31Oct95		WIRE RANGE 絶縁電線断面規格		INSULATION DIA 絶縁外径	
DIMENSIONS: 単位: ㎜ mm		TOLERANCES UNLESS OTHERWISE SPECIFIED 公差 10 > : ±0.2 30 > : ±0.25 100 > : ±0.3 ANGLE : ±0.3°		Tyco Electronics Tyco Electronics Corporation Kawasaki, Japan		NAME 名称 MINI UMNL PLUG CABLE CLAMP ミニユニバーサルメイトロック プラグ ケーブル クランプ	
MATERIAL 材質 66NYLON V-0 W/G 20% BLACK		FINISH 仕上		SIZE A3		CAGE CODE 00779	
CUSTOMER DRAWING		DRAWING NO 番号 316454		SCALE 尺度 2:1		SHEET 枚数 1 OF 1 REV A1	