





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS | | | |
|-----|------|-------------|---------------------------|-----------|-------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| AD | 39 | J | REVISED PER ECO-15-008006 | 17NOV2015 | NK MM |

- 1 NO OF POSITIONS INDICATED PERTAINS TO THE HOUSING.
- 2 THIS COVER IS TO BE USED WITH 102536 .
- 3 MATERIAL: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK.



| | | | | | |
|----------|------------------|--------------|----|------------|-------------|
| OBSOLETE | 91.44[3.600] | 88.90[3.500] | 35 | 72 | -3-102540-4 |
| OBSOLETE | 88.90[3.500] | 86.36[3.400] | 34 | 70 | -3-102540-3 |
| OBSOLETE | 86.36[3.400] | 83.82[3.300] | 33 | 68 | -3-102540-2 |
| OBSOLETE | 83.82[3.300] | 81.28[3.200] | 32 | 66 | -3-102540-1 |
| OBSOLETE | 81.28[3.200] | 78.74[3.100] | 31 | 64 | -3-102540-0 |
| OBSOLETE | 78.74[3.100] | 76.20[3.000] | 30 | 62 | -2-102540-9 |
| OBSOLETE | 76.20[3.000] | 73.66[2.900] | 29 | 60 | -2-102540-8 |
| OBSOLETE | 73.66[2.900] | 71.12[2.800] | 28 | 58 | -2-102540-7 |
| OBSOLETE | 71.12[2.800] | 68.58[2.700] | 27 | 56 | -2-102540-6 |
| OBSOLETE | 68.58[2.700] | 66.04[2.600] | 26 | 54 | -2-102540-5 |
| OBSOLETE | 66.04[2.600] | 63.50[2.500] | 25 | 52 | -2-102540-4 |
| OBSOLETE | 63.50[2.500] | 60.96[2.400] | 24 | 50 | -2-102540-3 |
| OBSOLETE | 60.96[2.400] | 58.42[2.300] | 23 | 48 | -2-102540-2 |
| OBSOLETE | 58.42[2.300] | 55.88[2.200] | 22 | 46 | -2-102540-1 |
| OBSOLETE | 55.88[2.200] | 53.34[2.100] | 21 | 44 | -2-102540-0 |
| OBSOLETE | 53.34[2.100] | 50.80[2.000] | 20 | 42 | -1-102540-9 |
| OBSOLETE | 50.80[2.000] | 48.26[1.900] | 19 | 40 | -1-102540-8 |
| OBSOLETE | 48.26[1.900] | 45.72[1.800] | 18 | 38 | -1-102540-7 |
| OBSOLETE | 45.72[1.800] | 43.18[1.700] | 17 | 36 | -1-102540-6 |
| OBSOLETE | 43.18[1.700] | 40.64[1.600] | 16 | 34 | -1-102540-5 |
| OBSOLETE | 40.64[1.600] | 38.10[1.500] | 15 | 32 | -1-102540-4 |
| | 38.10[1.500] | 35.56[1.400] | 14 | 30 | 1-102540-3 |
| | 35.56[1.400] | 33.02[1.300] | 13 | 28 | 1-102540-2 |
| | 33.02[1.300] | 30.48[1.200] | 12 | 26 | 1-102540-1 |
| | 30.48[1.200] | 27.94[1.100] | 11 | 24 | 1-102540-0 |
| | 27.94[1.100] | 25.40[1.000] | 10 | 22 | 102540-9 |
| | 25.40[1.000] | 22.86[.900] | 9 | 20 | 102540-8 |
| | 22.86[.900] | 20.32[.800] | 8 | 18 | 102540-7 |
| | 20.32[.800] | 17.78[.700] | 7 | 16 | 102540-6 |
| | 17.78[.700] | 15.24[.600] | 6 | 14 | 102540-5 |
| | 15.24[.600] | 12.70[.500] | 5 | 12 | 102540-4 |
| | 12.70[.500] | 10.16[.400] | 4 | 10 | 102540-3 |
| | 10.16[.400] | 7.62[.300] | 3 | 8 | 102540-2 |
| | 7.62[.300] | 5.08[.200] | 2 | 6 | 102540-1 |
| | C MAX | B | A | REF. 1 | PART NUMBER |
| | COVER DIMENSIONS | | | NO OF POSN | |

THIS DRAWING IS A CONTROLLED DOCUMENT.

| | | | |
|----------------------------|--|--|---|
| DIMENSIONS: mm [INCHES] | TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± - FINISH | DWN RAGHAVENDRA 06MAR09 CHK JEFFREY GESFORD 06MAR09 APVD JEFFREY GESFORD 06MAR09 PRODUCT SPEC - APPLICATION SPEC - WEIGHT - | NAME COVER - HALF, LOW PROFILE MASS TERMINATION AMPMODU, .100CL, FULL BAR POLARIZATION |
| MATERIAL 3 | | CUSTOMER DRAWING | SIZE A2 CAGE CODE 00779 DRAWING NO C=102540 RESTRICTED TO - SCALE 5:1 SHEET 1 of 1 REV J |