


DESIGNED FOR USE WITH .085 SEMI-RIGID CABLE	REV.	REVISIONS DESCRIPTION	DATE	APPROVED
CABLE ENTRY DIAMETER MINIMUM	040	REVISED PER ECN 95-0224	6/1/95	<i>MMA</i>
HOUSING	.088			
CONTACT	.021			



COPY IN PUERTO RICO

BEFORE CRIMPING	.465 REF (11.8 mm)	.348 REF (8.8 mm)
AFTER CRIMPING	.393 REF (10.0 mm)	.278 REF (7.1 mm)
	DIM "A"	DIM "B"

HOUSING COUPLING NUT BUSHING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B- 197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A

COMPONENT	MATERIAL	FINISH
-----------	----------	--------

NOTES:

1. CAPTURED CENTER CONTACT
2. PICTORIAL VIEW IS AFTER CRIMPING
3. MIN STRAIGHT CABLE LENGTH: .175
4. IT IS SUGGESTED TO BEND CABLE PRIOR TO CRIMPING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY R.GERAS	DATE 10-2-85		M/A-COM, Inc. Waltham, MA 02254
	CHECKED BY R.GERAS	DATE 10-2-85		
FRAC. • 1/64	DEC. • .005	ANGLES • 1°	APPRO'D BY R.GERAS	DATE 10-2-85
These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of items without written permission.	USE ASSY PROCEDURE	TITLE OSM STRAIGHT CABLE PLUG - COMPRESSION CRIMP ATTACHMENT M39012/79B3103		
	NO. AP. 20-583	SIZE B	CODE IDENT NO. 26805	REV 040
		SCALE 6:1	2001-8981-92	SHEET 1 OF 1

Customer 1050812 Rev 0  
Sheet 1 of 1