







		A/R	—	80665—1	INHIBITOR	3
		1	—	109435—1	WEDGE	2
		1	—	276914—1	BODY	1
		—1	DWG SIZE	PART NO	DESCRIPTION	ITEM NO
		—	← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)			
QTY REQD PER ASSY			PARTS LIST			

DRAWN BY:		14/OCT/98		MATERIAL		- HEAT TREAT	
D.RENNOX		CHECKED BY:		10/NOV/97		NONE	
H.HENRY		APPROVED BY:		10/NOV/97		 TE Connectivity	
P.CHAN		NAME		CONNECTOR, 1272KCMIL TO 954KCMIL, 1590 SERIES, YELLOW CODED, IMPACT			
SCALE		SIZE		DRAWING NO		SHEET	
1:1		A2		109433		1 OF 1	
REV						0	

DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	± .	1 PLC	± .
1 PLC	± .	2 PLC	± .03
2 PLC	± .005	3 PLC	± .0005
3 PLC	± .0005	4 PLC	± .0005

0	INITIAL RELEASE PER EC LC00-0122-97	100CT97	DR	PC
P	LTR	DATE	DWN	APVD
REVISION RECORD				