




PN 0-2 AS SHOWN

PN 0-5 AS SHOWN








PN 0-4 AS SHOWN

NOTES

TOOLS:



1 MATERIAL: HOUSING - ALUMINIUM DIECASTING ALLOY


2 SURFACE: VARNISH BLACK

3 PACKAGING: QUANTITY 3 PIECES IN A BOX


HYDR. HAND TOOL 60 kN 0-1110956-1


HEX.DIE. DIN 48083 70 qmm 0-1110956-3


HEX.DIE. DIN 48083 95 qmm 0-1110956-3




NUT FOR RETAINING WASHER









0-1102830-2
HF.13-STI-M10-A

0-1102830-3
HF.13-STI-C-S01

0-1102830-4
HF.13-BU-M10-A


0-1102830-5
HF.13-STI-C-S02

1	3	1	1	PIN CONTACT	COPPER	SILVER PLATED	5	WIRE SIZE 95mm ²
				CANTED COIL SPRING	BE-CU	SILVER PLATED	4	MOUNTED
				PIN CONTACT	COPPER	SILVER PLATED	3	WIRE SIZE 70mm ²
				PIN CONTACT	BRASS	SILVER PLATED	2	WITH SCREW BOLT M10
	1			SOCKET CONTACT	BRASS	SILVER PLATED	1	WITH SCREW BOLT M10
0-5	0-4	0-3	0-2	DESCRIPTION	MATERIAL	SURFACE	ITEM	NOTES
				HF.13-STI-M10				
				HF.13-STI-C-70mm ²				
				HF.13-BU-C-70mm ²				
				HF.13-BU-C-95mm ²				

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±1°

FINISH

DWN

25JAN2008

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco

Electronics

tyco Electronics AMP GmbH

53819 Neunkirchen (Germany)

NAME

CONTACT SYSTEM

SERIES HF 13

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

© 1102830

SCALE 2:1

SHEET 1 OF 1

REV B1

AMP 1471-9 REV 31MAR2000

Pro/ENGINEER DRAWING