




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A9	ECR-10-007735	01SEP2010	RK	SRE
	A10	REVISED PER ECR-17-014011	17JAN2018	SRG	MKO



NOTES

1 MATERIAL AND COLOR: SEE TABLE

FOR PN 0-7



	10	HA 10	1-0	57	70	81	NBR 60-70 SHORE,1mm THICK COLOR BLACK,ONE SIDE ADHESIVE
	9	HA 16	0-9	74	86	96	EPDM 69,CONDUCTIVE COLOR BLACK
	8	HA 10	0-8	57	70	81	
	7	HA 10	0-7	57	70	81	NBR 60-70° SHORE,1mm THICK COLOR BLACK,BOTH SIDES PLAIN
	6	HA 16	0-6	74	86	96	FKM 70° SHORE (VITON),-30°C TO +200°C 3mm THICK,COLOR BLACK
OBSOLETE	5	HA 10	0-5	57	70	81	
	4	HA 16	0-4	74	86	96	NBR 60-70 SHORE,1mm THICK COLOR BLACK,BOTH SIDES PLAIN
	3	HA 10	0-3	57	70	81	
	2	HA 16	0-2	74	86	96	ZELKAUTS CHUCK "B",ONE SIDE ADHESIVE 2.5mm THICK,COLOR BLACK
OBSOLETE	1	HA 10	0-1	57	70	81	

SI NO	TYPE	PART NO	A	B	C	MATERIAL
						1

2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

BY -

© COPYRIGHT 2000

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	n.ISO 8015: n.ISO 2768-mH-E: n.DIN 16901-120
1 PLC	±	
2 PLC	±	
3 PLC	±	
4 PLC	±	
ANGLES	±	



DWN 05.06.2001

SCHNEIDER

CHK 05.06.2001

SCHWEIGER

APVD 05.06.2001

T.SCHNURPFIL

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

MATERIAL



FINISH



TE Connectivity

NAME FLANGE MOUNTED SEAL
SERIES HA 10/16

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A 4	00779	C=1106350	

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV A10