


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		A1	ECR-06-022445	20SEP06	MH	CN
			B	ECR-08-021872	26AUG08	PK	PB
			B1	ECR-10-022205	23MAY11	KK	HMR

ITEM NO	PART NUMBER	APPROVED ALTERNATIVE PART NUMBER	DESCRIPTION	QTY/ ASSY
1	1-1337428-0	6-1337428-0	75 ohm BNC STRAIGHT PLUG	1
2	1337767-2	N/A	STRAIN RELIEF	2
3	1337715-2	N/A	RG59B/U CABLE	A/R
4	1-1337525-0	N/A	75 ohm BNC ELBOW PLUG	1



1500 ±25	1337778-4	
1000 ±25	1337778-3	OBSOLETE
500 ±12	1337778-2	
250 ±10	1337778-1	OBSOLETE
DIM 'A'	TE PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.CHURCHILL 21DEC2000	STE TE Connectivity	
DIMENSIONS: mm		CHK D.CHICK 21DEC2000		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. JEWELL 21DEC2000	NAME BNC PLUG - BNC PLUG CABLE ASSEMBLY	
0 PLC ± -		PRODUCT SPEC -	APPLICATION SPEC -	
1 PLC ± 0.1		WEIGHT -	SIZE A3	CAGE CODE 00779
2 PLC ± 0.01		DRAWING NO C-1337778		RESTRICTED TO -
3 PLC ± 0.001		CUSTOMER DRAWING		
4 PLC ± 0.0001		SCALE NTS		SHEET 1 OF 1
ANGLES ± -		REV B1		
FINISH -				