

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
HC	00	P	LTR	DESCRIPTION	DATE	APVD
			0	RELEASE PER EC 0514-0129-05	3/28/05	DC DC

D

C

B

A

D

C

B

A




1408492

1408492-1

PART NO

HOUSING	STAINLESS STEEL	PASSIVATE
CONTACT	BERYLLIUM COPPER	GOLD
DIELECTRIC	PTFE	N/A
COMPONENT	MATERIAL	FINISH

- NOTES:
- 1) IMPEDANCE: 50 OHMS
 - 2) FREQUENCY: 0-6 GHz
 - 3) VSWR: 1.35 MAX
 - 4) INSERTION LOSS: 0.07 f(GHz) dB MAX
 - 5) VOLTAGE RATING: 500 VEFF MAX
 - 6) DIELECTRIC WITHSTANDING VOLTAGE: 1000 VEFF MIN
 - 7) INSULATION RESISTANCE: 5000 MOhms MIN
 - 8) CENTER CONTACT CAPTIVATION:
AXIAL: 27 N MIN (BOTH DIRECTIONS)
TORQUE: 2.8 N-cm



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	31MAR2003	tyco Electronics Tyco Electronics Corporation Norwood, MA 02062		
DIMENSIONS: MM		CHK	12/16/04			
		DCam	12/16/04	NAME SMA EDGE MOUNT JACK RECEPTACLE - STRAIGHT TERMINAL		
		APVD	12/16/04			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DCam	12/16/04	SIZE A2		
0 PLC ± -		PRODUCT SPEC				
1 PLC ± -		APPLICATION SPEC		CAGE CODE 00779		
2 PLC ± -						
3 PLC ± 0.13				DRAWING NO 1408492		
4 PLC ± -						
ANGLES ± 1				RESTRICTED TO -		
FINISH						
MATERIAL		WEIGHT	-	SCALE 10:1		
-						
		CUSTOMER DRAWING		SHEET 1 OF 1		
				REV 0		