


DWG NO  
1474482

DIMENSIONS AND TOLERANCES PER ASME Y14.5M (2009 EDITION). THIS DRAWING IS A CONTROLLED DOCUMENT.



NOTES:

- ① MUST BE PACKAGED IN SETS OF 16 JUMPERS PER PACKAGE IN A MANNER WHICH WILL PREVENT THE LEADS FROM BEING BENT OR OTHERWISE DAMAGED.
- ② MUST BE PACKAGED IN SETS OF 1 JUMPER PER PACKAGE IN A MANNER WHICH WILL PREVENT THE LEADS FROM BEING BENT OR OTHERWISE DAMAGED.
- ③ PARTS WERE SIMILAR TO LISTED T&B PART NUMBERS EXCEPT FOR PIN LENGTH AND PACKAGING.

		4.49±.76 [.177±.030]	91.44 [3.600]	13	FST-23.6A-13, PIN LENGTH = .177, SP PKG	3-1437193-7
①	FS1400740	4.45±.76 [.175±.030]	64.77 [2.550]	25	FST-22.55A-25, PIN LENGTH = .175, SP PKG	1-1437179-4
②	FST140585504	4.06±.76 [.160±.060]	106.68 [4.200]	13	FST-24.2A-13, PIN LENGTH = .160, SP PKG	4-1437193-0
②	FST140585503	4.06±.76 [.160±.060]	101.6 [4.000]	12	FST-24A-12, PIN LENGTH = .160, SP PKG	3-1437193-9
②	FST40585502	4.06±.76 [.160±.060]	96.52 [3.800]	12	FST-23.8A-12, PIN LENGTH = .160, SP PKG	3-1437193-8
②	FST40585501	4.06±.76 [.160±.060]	91.44 [3.600]	13	FST-23.6A-13, PIN LENGTH = .160, SP PKG	1474498-1
	WAS T&B P/N	"L"	"B"	"N"	DESCRIPTION	TYCO ELECTRONICS P/N

③

NO. COND.

CUSTOMER DRAWING

DWN J. SCHWARTZ	04/SEP/01	MATERIAL -	HEAT TREAT -
CHK J. MONTGOMERY	4SEP01		
APVD J. MONTGOMERY	4SEP01		
NAME FLEXSTRIP, FST, SPECIAL			
SCALE N.T.S.	SIZE A3	DRAWING NO 1474482	SHEET 1 OF 1
		REV G	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

LOC	---
DIST	---

G	PER ECO-12-010762	29/MAY/12	DWD	LER
P	LTR	REVISION RECORD	DATE	DWN
			APVD	

DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± 0.2	
		1 PLC ± 0.1	
		2 PLC ± 0.05	
		3 PLC ± -	
		4 PLC ± -	
ANGLES ±		-	
SURFACE TEXTURE			

3306-7 (1/08)

8 | 7 | 6 | 5 | 4 | 3 | 2 | 1