


D


C

B


A




9 POSITION




15 POSITION




37 POSITION



51 POSITION




65 POSITION



2X $\phi .050 \pm .002$ (FOR 1.0mm MTG SCREW)
 $\phi .058 \pm .002$ (FOR 1.2mm MTG SCREW)
 $\phi \phi .004$

TYPICAL PCB LAYOUT
SIZE 25 SHOWN FOR REFERENCE



1589602

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .010
3 PLC ± .005
4 PLC ± -
ANGLES ± 1°
FINISH
SEE NOTE

DWN
M. STORRY
06-07-00

CHK
S. KAIN
06-07-00

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
RECEPTACLE ASSEMBLY, HORIZONTAL MOUNT,
THROUGH HOLE, 2 TO 4 ROW, .050 SPACING,
PLASTIC OR METAL, .125 LEAD LENGTH

SIZE
A2

CAGE CODE
OPJN9

DRAWING NO
C=1589602

RESTRICTED TO
-

SCALE
8:1

SHEET
2 of 2

REV
E