



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | G2  | REVISED PER ECR-23-171745 | 18APR2023 | DB  | DH   |
|           | G3  | REVISED PER ECN-23-236544 | 27OCT2023 | WLS | RE   |

- △1 SPLICE FREE, FOR AMP\_O\_MATOR.
- △2 REELED WITH PAPER LAYER.
- △3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CHAMFER



|    |                 |                |    |             |
|----|-----------------|----------------|----|-------------|
| △3 | TIN             | BRASS          | △2 | 6-160316-4  |
|    | TIN-LEAD        | PHOSPHORBRONZE |    | 6-160316-3  |
| △3 | TIN-LEAD        | BRASS          |    | 6-160316-2  |
| △3 | PRE-TIN HOT DIP | PHOSPHORBRONZE |    | 6-160316-0  |
| △3 | TIN             | BRASS          | △1 | 5-160316-9  |
| △3 | NONE            | BRASS          | △1 | 5-160316-8  |
|    | GOLD            | PHOSPHORBRONZE |    | 5-160316-7  |
| △3 | TIN             | PHOSPHORBRONZE |    | 5-160316-6  |
|    | NONE            | PHOSPHORBRONZE |    | 5-160316-5  |
| △3 | GOLD            | BRASS          |    | 5-160316-4  |
|    | SILVER          | BRASS          |    | 5-160316-3  |
|    | TIN             | BRASS          | △2 | 5-160316-2  |
|    | NONE            | BRASS          |    | 5-160316-1  |
|    | FINISH          | MATERIAL       |    | PART NUMBER |

|  |                           |                    |          |                                    |            |
|--|---------------------------|--------------------|----------|------------------------------------|------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                           | DWN<br>D.KESSLER   | 11-04-94 | <b>STE</b> TE Connectivity         |            |
| DIMENSIONS:<br>mm [INCHES]             |                           | CHK<br>P.BEIJNON   |          |                                    |            |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |                           | APVD<br>L.V. SOEST |          | NAME<br>.110 SRS FASTON RECEPTACLE |            |
| 0 PLC ± 1.0                            |                           | PRODUCT SPEC       |          | SIZE                               |            |
| 1 PLC ± 0.5                            |                           | APPLICATION SPEC   |          | CAGE CODE                          | DRAWING NO |
| 2 PLC ± 0.2                            |                           |                    |          | W300779                            | C-160316   |
| 3 PLC ± -                              |                           |                    |          | RESTRICTED TO                      |            |
| 4 PLC ± -                              |                           |                    |          | -                                  |            |
| ANGLES ± 1°                            |                           | WEIGHT             |          | SCALE 6:1 SHEET 1 OF 1 REV G3      |            |
| FINISH                                 |                           |                    |          | CUSTOMER DRAWING                   |            |
| WIRE RANGE :                           | INSUL-RANGE :             |                    |          |                                    |            |
| 0.3-0.56mm <sup>2</sup><br>(22-20 AWG) | ∅ 1.0-2.0<br>(∅.050-.080) |                    |          |                                    |            |