


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
J			0	RELEASED	FJD0-0076-04	08MAR2004	E.T	Y.K



① COVER HSG

③ CABLE CLUMP

② RELEASE PLATE

-1:AS SHOWN

I THIS DRAWING IS DESCRIBED CABLE CONN I IROW CHICKLET WAFER TYPE ASSEMBLY KIT. (TYCOP/N 1674587-1)

TABLE I

QTY	MATERIAL	NAME	ITEM
2	PA	TIE WRAP	
2	SUS	CROSS RECESSED HEAD MACHINE SCREW WITH WASHER, M3x4mm	
2	POLYETHYLENE TEREPHTHALATE FILM	PULL TAB	
2	SUS	CABLE CLAMP	③
1	SUS	RELEASE PLATE	②
1	GLASS FILLED PBT	COVER HSG	①

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN E. TAKEMASA 08MAR2004	Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位: 絶 mm		CHK M. KIMURA 08MAR2004	NAME CABLE CONN I IROW CHICKLET WAFER TYPE ASSEMBLY KIT	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 0 PLC ± 10 > ± 0.2 1 PLC ± 30 > ± 0.25 2 PLC ± 100 > ± 0.3 3 PLC ± 4 PLC ± ANGLES ± FINISH 仕上		APVD Y. KASHIWA 08MAR2004	RESTRICTED TO -	
MATERIAL 材料 SEE TABLE I		PRODUCT SPEC 製品規格	SIZE A2	CAGE CODE 00779
		APPLICATION SPEC 取付適用規格	DRAWING NO. 1674587	REV 0
		WEIGHT	CUSTOMER DRAWING	