



LOC	DIST	REVISIONS			
GA	1	P	LTR	DESCRIPTION	DATE
		A		INITIAL REL. PER LC20-0044-09	20MAY2009
					DM
					BJ



SECTION A-A

1. ACCOMMODATES:
 750 KCMIL STD STR-COMPRESSED
 (.998-.968 DIA) TO 500 KCMIL STD
 STR-COMPRESSED (.813-.789 DIA) COPPER
 CONDUCTORS.



MARKING:



CKSR075S050TNT
 750 KCMIL
 500 KCMIL
 CSA 30 CU
 [DATE CODE]



FINISH:

ELECTRO-TIN PLATED.



ALL DIMENSIONS ARE FOR REFERENCE ONLY.



DO NOT CRIMP BETWEEN SCRIBE LINES.

CKSR075S050TNT	1710664-1
CATALOGUE NO.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MURUGIAH 20MAY2009	Tyco Electronics Tyco Electronics Corporation Markham, ON L3R-1E1	
DIMENSIONS: INCHES		CHK A. BULZA 22MAY2009		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B. JOHNSON 22MAY2009	NAME COPPER COMPRESSION REDUCING SLEEVE, SOLID OIL STOP, TIN PLATED, 750 KCMIL TO 500 KCMIL COPPER CONDUCTORS	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		
MATERIAL ETP COPPER	FINISH 3	SIZE A3	CAGE CODE 00779	DRAWING NO 1710664
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1
			REV A	