



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

REVISIONS						
P	LTR	DESCRIPTION	DATE	DWN	APVD	
C		LC20-0056-12 / ECO-12-010512	28MAY2012	DM	BJ	
D		LC20-0031-16 / ECO-16-005675	14APR2016	DM	BJ	
E		LC20-0085-16 / ECO-16-011010	21JUL2016	DM	BJ	
E1		LC20-0020-17 / ECO-17-001984	21FEB2017	DM	BJ	
F		LC20-0060-19 / ECO-19-010173	29JUN2019	DM	BJ	



1. BODY STRENGTH: 10,000 lbs.
PULLING EYE STRENGTH: 6000 lbs.
2. BLADE DETAIL MAY NOT BE EXACTLY AS SHOWN.
3. 1710736-1 WILL BE REPLACED BY 1710736-5 IN THE FUTURE.

40,000 AMPERE RMS ASYMMETRICAL	25,000 AMPERE RMS SYMMETRICAL	900 AMPERE RMS	60 HERTZ	350 kV	69 kV AC
MOMENTARY CURRENT	THREE SECOND CURRENT	CONTINUOUS CURRENT ALLOWABLE RATING: (PER ANSI C37-32.3.2.1 2002)	FREQUENCY	BASIC IMPULSE INSULATION LEVEL (BIL)	VOLTAGE
SHORT TIME CURRENT					
RATINGS					

X-SMALL	1710736-5
X-SMALL	1710736-4
X-LARGE	1710736-3
LARGE	1710736-2
SMALL	1710736-1
YOKE SIZE IN ILD ASSEMBLY	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D. MURUGIAH
12FEB2010

CHK
S. KAMEL
29MAR2010

APVD
B. JOHNSON
29MAR2010

TE Connectivity

NAME
INLINE DISCONNECT SWITCH ASSEMBLY WITHOUT TAPS, AMPACT, 69 kV, 900 Amp

PRODUCT SPEC

APPLICATION SPEC

SIZE
A2

CAGE CODE
00779

DRAWING NO
1710736

RESTRICTED TO

WEIGHT
0

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 of 1

REV
F