


寸法公差は±0.20
(TOLERANCE: ±0.2)
パネル取付穴
(DIMENSION OF PANEL)



NOTES:

1. APPLIED CONTACT P/N: 170359, 170360, 170361, 170362
 2. MATING CONN: PLUG HOUSING P/N 172339
 3. PANEL THICKNESS: 0.8 ~ 2.0 mm
 4. PRESS DIRECTION OF PANEL MUST BE SAME AS HOUSING INSERTED DIRECTION.
 5. INSTRUCTION SHEET: IS-105J
 6. PRODUCT SPEC: 108-5151
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

注:

1. 使用端子型番は、170359, 170360, 170361, 170362
2. 嵌合相手ハウジング型番は、172339
3. 適用パネル厚 0.8 ~ 2.0 mm.
4. 取付穴打抜方向とハウジングの挿入方向は同じとする。
5. 取扱説明書: IS-105J
6. 適用製品仕様書: 108-5151

OBSOLETE	黄 (YELLOW)	1- 172331 - 4
	黒 (BLACK)	1- 172331 - 9
	青 (BLUE)	1- 172331 - 6
	緑 (GREEN)	1- 172331 - 5
	赤 (RED)	1- 172331 - 2
	自然色 (NATURAL)	172331 - 1
色 (COLOR)		型番 (P/N)

材料 (MATERIAL) 6/6 ナイロン (UL94V-2) (NYLON 6/6 UL94V-2)	一般公差 TOLERANCE ± 0.3 EXCEPT ± 1° AS NOTED	STE TE Connectivity
仕上 (FINISH) 色: 表参照 HOUSING COLOR: SEE TABLE	DR. <i>Ryusa Yoda</i> CHK. <i>Tanipawa</i> DE. <i>u/21 st</i> APP.	
名称 (NAME): MINI-UNIVERSAL MATE-N-LOK CONN. CAP HOUSING 6Pos: (UL94V-2) 6極 ミニユニバーサル マチンロック コネクターハウジング (UL94V-2)		SIZE LOC 番号 (NO.) B J C-172331
尺度 (SCALE) 2:1		REV. B SHEET 1/1

(CUSTOMER DRAWING) 参 考 図 面

単位: 概 寸法 DIMENSIONS IN MM. DO NOT SCALE PRINT

B	REVISED PER ECR-19-001522	BDA	SG	03MARCH09
A3	REVISED PER ECO-11-005030	RK	HMR	01APR11
LTR.	変更 (REVISION RECORD)	DR.	CHK.	DATE