






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B2		OBSOLETE 2--1	ECR-16-003196	17AUG16	KF HY



- 1. 取付ネジ: M3X5 (4カ所)
 - 2. 適用基板厚: 1.6
 - △回路NO: 下図参照
-
- 1. MOUNTING SCREW: M3X5 (4 PLC)
 - 2. PCB THICKNESS: 1.6
 - △CIRCUIT NO:



プリント基板取付穴位置寸法 (TOLERANCE: ±0.1)
 MOUNTING DIMENSION FOR PCB (公差: ±0.1)

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差

0 < x ≤ 10	±0.2
10 < x ≤ 30	±0.25
30 < x ≤ 100	±0.3
ANGLE	±3°

SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 42	1~42 (全極)	-	NATURAL 自然色	2-5174480-1
SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 9	6,7,14~16,18,32,36,37 (9極)	1~5,8~13,17,19~31, 33~35,38~42 (33極)	NATURAL 自然色	1-5174480-1
PRE-TIN × 33					
TIN-LEAD	SELECTIVE GOLD × 42	1~42 (全極)	-	NATURAL 自然色	2-174480-1
TIN-LEAD	SELECTIVE GOLD × 9	6,7,14~16,18,32,36,37 (9極)	1~5,8~13,17,19~31, 33~35,38~42 (33極)	NATURAL 自然色	1-174480-1
PRE-TIN × 33					
PRE-TIN × 42			1~42 (全極)	NATURAL 自然色	174480-1
SOLDERING SIDE 半田付け面	CONTACT SIDE 接触部側	△3 GOLD PLATED CIRCUIT NO. 全めっき回路番号	△3 PRE-TIN CIRCUIT NO. 全めっき回路番号	COLOR 色	PART NUMBER 製品型番
CONTACT FINISH コンタクト仕上					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN K.FURUYAMA 21APR2015		42POSITION CAP HOUSING ASSEMBLY 070 SERIES MULTI LOCK I/O CONNECTOR	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
CHK Y.MITO 21APR2015			A2	00779	C=174480	-	
APVD R.KOMIYAMA 21APR2015			WEIGHT	26.9 g		SCALE	2:1
PRODUCT SPEC 製品規格			CUSTOMER DRAWING		SHEET	1 of 1	REV
APPLICATION SPEC 取付適用規格							