



REVISIONS	DESCRIPTION	DATE	DWN	APP'D
0		28APR05	HXF	DF

200mm

20mm REF



2.0 MAX



- NOTES:
1. HIROSE COMPATIBLE
 2. 100% ELECTRICAL TESTING FOR: CONTINUITY AND SHORTS. HI-POT AT 150 VDC FOR 100ms
FREQUENCY RANGE: DC TO 6 GHZ
VSWR 1.4:1 MAX
 3. PRODUCT RATINGS:
TEMPERATURE: -40 TO +90 DEG.C
VOLTAGE: 60 VAC
CHARACTERISTIC IMPEDANCE: 50 OHMS
UMCC MATING DURABILITY: 30 CYCLES
MCX MATING DURABILITY: 500 CYCLES

QTY	UNIT	DESCRIPTION	ITEM
1	PC	TUBING, HEAT SHRINK	3
1	MM	MINIATURE COAX CABLE, 0.80mm OD	2
1	PC	MCX R/A PLUG FOR 0.80 OD CABLE	1
1	PC	UMCC TYPE II PLUG	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	Hao Xiangfeng	28APR05	tyco	Tyco Electronics Corporation
CHK	Paul Zhou	28APR05	Electronics	KunShan, CHINA 215321
APP'D	DENVER WILSON	28APR05		
PRODUCT SPEC				
APPLICATION SPEC				
WEIGHT				

DIMENSIONS:	MM	TOLERANCE UNLESS OTHERWISE SPECIFIED:	SIZE	DATE	DRAWING NO	RESTRICTED TO
0. PLC		±	A4	00779	1750110-7	
1. PLC		±				
2. PLC		±				
3. PLC		±				
4. PLC		±				
ANGLES		±				
MATERIAL						