





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
J	—	C6	REVISED PER ECR-19-017851	26NOV2019	SM	DZ
		D	REVISED PER ECR-19-017623	17DEC2020	MG	DZ



- 1. APPLICABLE CONTACT PART NUMBER;  
 REC CONTACT: 175152-□ (#20-#16AWG)  
 175151-□ (#26-#22AWG)
- 2. TO BE USED WITH THE CONTACT WHICH IS RATED 105°C MAX
- 3. MATERIAL: PA66, UL94 V-0, GWIT 775°C

1-176282-5	130°C MAX	△3	GREEN 绿	2	1-176271-5
1-176282-1	130°C MAX	△3	NATURAL 自然色		1-176271-1 <sub>△2</sub>
176282-□ 176292-□	105°C MAX	PA66	BLACK 黒	2	176271-9
			BLUE 青		176271-6
			YELLOW 黄		176271-4
			RED 赤		176271-2
NATURAL 自然色				176271-1	
MATING CONN. PART NUMBER 嵌合相手型番	TEMPERATURE RATING 定格温度	TYPE 種類	HOUSING COLOR 色	Pos. 極数	PART NUMBER 型番
MATERIAL 材料					

- 1. 適用端子型番;  
 リセコンタクト: 175152-□ (#20-#16AWG)  
 175151-□ (#26-#22AWG)
- 2. 適用コンタクトの使用温度は最大105°C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.SHINDO 08NOV1989	<b>TE</b> TE Connectivity		
DIMENSIONS: mm		CHK Y.FUJITA 08NOV1989			
TOLERANCES UNLESS OTHERWISE SPECIFIED: $\leq 10$ ± 0.2 $10 < \leq 30$ ± 0.25 $30 <$ ± 0.3		APVD Y.FUJITA 08NOV1989	NAME AMP UNIVERSAL POWER CONN. 3.96mm PITCH PLUG HOUSING 2 Pos. (SGL ROW) AMP ユニバーサルパワーコネクタ 2極 3.96mmピッチ キャップハウジング		
ANGLES FINISH ± 3°		PRODUCT SPEC 108-5302	SIZE A3	CAGE CODE 00779	DRAWING NO C-176271
MATERIAL SEE TABLE		APPLICATION SPEC 114-5142	RESTRICTED TO —		
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV D