

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		NEW RELEASE	10MAR2015	RRN	PS

NOTES:

1. MATERIALS & FINISH
 HOUSING : PA HIGH TEMP 30GF V0, COLOUR: BLACK
 CONTACT : Cu ALLOY
 PLATING : LEAD FREE TIN OVER NICKEL UNDERPLATE

2. ELECTRICAL

RATED VOLTAGE: 300V
 RATED CURRENT: 12A
 CONTACT RESISTANCE: <15 mOhm
 INSULATION RESISTANCE: >1000 MOhm (500V DC)

3. OPERATING TEMPERATURE RANGE: -40 °C TO +110 °C

4 TOLERANCE NOT CUMULATIVE.

35.00	8	1986707-8
25.00	6	1986707-6
15.00	4	1986707-4
10.00	3	1986707-3
5.00	2	1986707-2
DIM OF "A"	NO OF POS.	PART NUMBER

-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±
	1 PLC ±0.2
	2 PLC ±0.15
	3 PLC ±
	4 PLC ±
	ANGLES ±°
MATERIAL	FINISH
SEE NOTE	-
-	-

DWN	10MAR2015
R R NAYAK	
CHK	13MAR2015
PRASHANTH S	
APVD	13MAR2015
PRASHANTH S	
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
Customer Drawing	

TE Connectivity		NAME	
		HEADER, SIDE STACKABLE, PITCH 5mm STRAIGHT, SMD	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	©=1986707	-
SCALE		SHEET	REV
6:1		1 OF 1	A

1470-19 (3/13)