

4

3

2

1

THIS DRAWING IS UNPUBLISHED.
VERTRÄULICHE UNVERÖFFENTLICHTE ZEICHNUNG

RELEASED FOR PUBLICATION
FREI FUER VERÖFFENTLICHUNG ,1998

MATED WITH:
PASSEND ZU:
ZL1

LOC AI
DIST -

REVISIONS
ÄNDERUNGEN

© COPYRIGHT 1998




BY TE INCORPORATED. ALL RIGHTS RESERVED.
ALLE RECHTE VORBEHALTEN

P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	A2	ECR-10-004359	09.03.10	GW	ST
	A3	ECR-10-014931	08.08.10	RK	GL

NOTES:

- ELECTRICAL DATA: CONTACT RESISTANCE: 10 mOhm MAX
INSULATION RESISTANCE: 100 MOhm MIN at 500VDC
CURRENT RATING: 5 AMPS
BREAKDOWN VOLTAGE: 500 VAC MIN PER MINUTE
- ENVIRONMENTAL: OPERATING TEMPERATURE CONNECTOR: -25°C TO +90°C
OPERATING TEMPERATURE CABLE: -40°C TO +150°C
SEALING REQUIREMENTS: IP67
- PROD SPEC: 108-3641
- PACKAGING: 107-3334
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QTY
1	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1
2	CONNECTOR BODY	POLYURETHANE	GREEN	1
3	PIN CONTACT	BRASS	0.15µm GOLD PLATED OVER NICKEL	4
4	4 CORE CABLE (CORES 20AWG)	XLPE JACKET HAL FREE	RED	1



M12 STRAIGHT MALE CONNECTOR 7.5m CABLE	1991118-1
DESCRIPTION	PART NUMBER

<p>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TE INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESES ZEICHNUNGSDOKUMENT WIRD DURCH TE INCORPORATED KONTROLLIERT. ÄNDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN. DEN JEWEILS LETZTIGUELITIGEN ÄNDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE.</p>		DWN G.WROBLEWSKI 16.05.08	<p>Tyco Electronics AMP GmbH D-53819, Neunkirchen, Germany</p>	NAME		
<p>DIMENSIONS: DIMENSIONEN: mm</p>		CHK T.SCHNURPFEIL 16.05.08		M12-STRAIGHT-MALE-CONNECTOR 4-POSITION, B-CODE, XL-PE-CABLE		
<p>TOLERANCES UNLESS OTHERWISE SPECIFIED:</p> <p>0 PLC # 1 PLC # 2 PLC # 3 PLC #</p> <p>ANGLES /WINKEL # FINISH /OBERFLÄCHE/FARBE</p>		APVD T.SCHNURPFEIL 16.05.08		PRODUCT SPEC PRODUKTSPEZ. -	SIZE A3	CAGE CODE 00779
MATERIAL		APPLICATION SPEC VERARBEITUNGSSPEZ. -	WEIGHT GEWICHT -	DRAWING NO ZEICHNUNGS-NR. G= 1991118	RESTRICTED TO NUR FUER -	
CUSTOMER DRAWING /KUNDENZEICHNUNG			SCALE MASSSTAB NS	SHEET BLATT 1 VON 1	OF 1	REV. A3