




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION JUN , 2008.
 © COPYRIGHT 2008 BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	/	P	LTR	DESCRIPTION	DATE	DWN	APVD
		B		REVISED ECR-10-016584	10AUG2010	T.T	T.M



- 1.一般公差：±0.25
- 2.材料：銅合金全面Niめっき1.3μm以上
接点部金めっき0.38μm以上めっき
- 3.適用電線：AWG#20-#16 (被覆外径φ1.8~φ3.23)

- 1.GENERAL TOLERANCE: ±0.25
- 2.MATERIAL: COPPER ALLOY, FINISH: OVER NI PLATING 1.3um MIN.
(CONTACT AREA) 0.38um MIN GOLD PLATING
- 3.APPLICABLE WIRE: AWG#20-#16 (INS DIA φ1.8~φ3.23)

2040015-2
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.URUSHIBATA 18JUN2008	Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: 単位： 耗 mm		CHK T.KUDO 18JUN2008	NAME S.MANABE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD S.MANABE 18JUN2008	PRODUCT SPEC 製品規格 108-78182	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC 取付適用規格 114-5369	SIZE A3	CAGE CODE 00779
MATERIAL 材料 COPPER ALLOY	FINISH 仕上	WEIGHT	DRAWING NO 番号 G-2040015	RESTRICTED TO
CUSTOMER DRAWING			SCALE 尺度 5:1	SHEET 1 OF 1
			REV B	