


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	B	ECR-14-016330	10NOV2014	HZ	RZ		

- ⚠ MATERIAL
- PROTECTIVE COVER: TPE, COLOR: BLACK, UL94 HB*
 - FERRULE SUBASSEMBLY: ZIRCONIA/METAL
 - COMPRESSION SPRING: STAINLESS STEEL
 - FRONT HOUSING: PEI, COLOR: BEIGE, UL94 V-0*
 - INNER TUBING: PTFE, COLOR: CLEAR, UL VW-1
 - REAR BODY: METAL
 - BEND LIMITING BOOT: PP, COLOR: BEIGE, UL94 V-0*
 - BOOT AND SHORT BUFFER BOOT: TPE, COLOR: BEIGE, UL94 V-0*
 - CRIMP EYELET/HEAT SHRINK ASSY: ALUM. ALLOY, HEAT SHRINK: POLYOLEFIN, UL VW-1
 - DUPLEX CLIP: PP, COLOR: BEIGE, UL94 V-0*
 - 3.0mm CRIMP EYELET: NICKEL PLATED BRASS
- *RATED AT QUALIFYING THICKNESS.

- INSTRUCTION SHEET: 408-8675 AVAILABLE FOR DOWNLOAD AT www.tycoelectronics.com/documents OR www.ampnetconnect.com/foguide.
- BULK PACKAGE.



DESCRIPTION	PART NUMBER
DUPLEX, 2.4mm JACKETED	2-2064938-4
DUPLEX, 3.0mm JACKETED	2-2064938-3
DUPLEX, 1.6-2.0mm JACKETED	2-2064938-2
DUPLEX, 900um BUFFERED	2-2064938-1
SIMPLEX, 2.4mm JACKETED	2064938-4
SIMPLEX, 3.0mm JACKETED	2064938-3
SIMPLEX, 1.6-2.0mm JACKETED	2064938-2
SIMPLEX, 900um BUFFERED	2064938-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN B. BRIGGS 31MAR2009	TE Connectivity
CHK S. MILLER 31MAR2009	
APVD D. BAECHTLI 31MAR2009	
NAME KIT, CONNECTOR, LC, MM, BULK PACK	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH
MATERIAL	PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING
SIZE: A200779 CAGE CODE: C-2064938 DRAWING NO: C-2064938 RESTRICTED TO: - SCALE: 3:1 SHEET 1 OF 1 REV B	