


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	ECR-21-117922	20OCT2021	DHC	AB



NOTES

- 1 PACKAGING:
ASSEMBLIES PACKED IN TE STANDARD BOXES WITH INTERMEDIATE LAYERS OF CORRUGATED PAPER OR PAPER STUFFING (TE SPEC. 107-18032). EACH ASSEMBLY ROLLED TO A RING AND WITH RUBBER STRING BONDED
- 2 100% ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857.3.1.1

BEMERKUNGEN

- 1 VERPACKUNG:
ASSEMBLIES IN TE STANDARDKARTON MIT ZWISCHENLAGEN (WELLPAPPE ODER PAPIERPOLSTERKISSEN) VERPACKEN (TE SPEZ. 107-18032). JEDES ASSEMBLY ZU EINEM RING GEWICKELT UND MIT GUMMI BAND GEBUNDEN.
- 2 100% ELEKTRISCHE PRUEFUNG NACH TE SPEZIFIKATION 108-18857.3.1.1

WIRING SCHEDULE:
BELEGUNGSPLAN:

CONNECTOR	COLOUR/FARBE
+	BROWN/BRAUN
-	BLUE/BLAU

LENGTH SCHEDULE: /Laengentabelle:

TE PART NO.	REV.	LENGTH L (mm)	TOL.	ASSEMBLY COLOR	
1-2083034-1	A	500	±20	BLACK	OBSOLETE
1-2083034-2	A	1000	±20	BLACK	
1-2083034-3	A	1500	±20	BLACK	
1-2083034-4	A	2000	±20	BLACK	
1-2083034-5	A	500	±20	WHITE	
1-2083034-6	B	1000	±20	WHITE	
1-2083034-7	B	1500	±20	WHITE	
1-2083034-8	B	2000	±20	WHITE	
2-2083034-1	A	500	±20	BLACK	OBSOLETE
2-2083034-2	A	1000	±20	BLACK	
2-2083034-3	A	1500	±20	BLACK	
2-2083034-4	A	2000	±20	BLACK	
2-2083034-5	B	500	±20	WHITE	OBSOLETE
2-2083034-6	B	1000	±20	WHITE	
2-2083034-7	A	1500	±20	WHITE	
2-2083034-8	B	2000	±20	WHITE	

OBSOLETE				OBSOLETE				OBSOLETE								DESCRIPTION	ITEM NO.								
SEE TABLE				-	-	-	-	SEE TABLE				-	-	-	-	H03VVH2-F 2x0.75mm ² , white	9								
-	-	-	-	SEE TABLE				-	-	-	-	SEE TABLE				H03VVH2-F 2x0.75mm ² , black	8								
1	1	1	1	-	-	-	-	1	1	1	1	-	-	-	-	Ring clip, white	7								
-	-	-	-	1	1	1	1	-	-	-	-	1	1	1	1	Ring clip, black	6								
1	1	1	1	-	-	-	-	1	1	1	1	-	-	-	-	Tube, white	5								
-	-	-	-	1	1	1	1	-	-	-	-	1	1	1	1	Tube, black	4								
2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	MQS pin contact	3								
1	1	1	1	1	1	1	1	-	-	-	-	-	-	-	-	Lighting system outlet, yellow LV-2	2								
-	-	-	-	-	-	-	-	1	1	1	1	1	1	1	1	Lighting system outlet, light grey LV-1	1								
QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY	QTY										
2	82	72	62	52	42	32	22	11	8	1	7	1	6	1	5	1	4	1	3	1	2	1	1		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 1°	DWN T.Burzynski 17NOV2009	 TE Connectivity Cable Assembly Mini HVL male to pigtail
		CHK S.Sedlakova 18NOV2009	
		APVD G.Lindemann 18NOV2009	
MATERIAL	FINISH	PRODUCT SPEC	
-	-	APPLICATION SPEC	SIZE A3
		WEIGHT	CAGE CODE 00779
			DRAWING NO C-2083034
			SCALE NTS
			SHEET 1 OF 1
			REV B2

CUSTOMER DRAWING