




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	15MAY2018	GCM	AP



- NOTES:
1. RATED POWER: 1W
  2. RESISTANCE RANGE( $\Omega$ ): 100K ~ 10M
  3. MAX. WORKING VOLTAGE. DC: 1600V. RMS: 1150V



2008

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

Tyco Electronics AMP GmbH

© COPYRIGHT 2008

THIS DRAWING IS UNPUBLISHED.

DIMENSIONS:		DWN	15MAY2018	MATERIAL	FINISH		
mm		GANESH C M		-	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	15MAY2018	<b>TE Connectivity</b>			
		ALLAN.P					
0 PLC $\pm 0.2$ 1 PLC $\pm 0.1$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $45^\circ$		APVD	15MAY2018	NAME HIGH VOLTAGE CHIP RESISTORS TYPE SMV1W			
		TONY.N					
		PRODUCT SPEC		-	SIZE	CAGE CODE	DRAWING NO
APPLICATION SPEC		-	A 4	00779	C-2176322		
WEIGHT		-	CUSTOMER DRAWING				SCALE 10:1
				SHEET 1 OF 1		REV A	