






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	I	INITIAL DRAWING.	25APR2017	JAB	ERL
	A1	REVISED PER ECN-25-313025	25MAR2025	JM	AP



ISOMETRIC VIEWS
SCALE 3:1



Z	PER DETAIL Z	WATER BLUE	2-2203577-0
N	PER DETAIL N	PASTEL GREEN	1-2203577-3
M	PER DETAIL M	PASTEL ORANGE	1-2203577-2
L	PER DETAIL L	CARMINE RED	1-2203577-1
K	PER DETAIL K	CURRY	1-2203577-0
I	PER DETAIL I	BEIGE	2203577-9
H	PER DETAIL H	HEATHER VIOLET	2203577-8
G	PER DETAIL G	BLUE GREY	2203577-7
F	PER DETAIL F	NUT BROWN	2203577-6
E	PER DETAIL E	LEAF GREEN	2203577-5
D	PER DETAIL D	CLARET VIOLET	2203577-4
C	PER DETAIL C	SIGNAL BLUE	2203577-3
B	PER DETAIL B	CREAM	2203577-2
A	PER DETAIL A	JET BLACK	2203577-1
KEY CODE	KEYING	CODING COLOR	PART NUMBER

SUPERSEDED BY X-2405505-X


1. 2203577-1 AS SHOWN.

MATERIAL, POLYESTER PBT, COLOR SEE TABLE.


FEMALE INTERFACE PER ISO-20860-1, ISO-20860-2, SAE/USCAR-17, SAE/USCAR-18.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.A.BAKER CHK E.R.LOVE APVD F.R.LOVE	25APR2017 18JUL2017 18JUL2017	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±.010 1 PLC ±.010 2 PLC ±.010 3 PLC ±.010 4 PLC ±.010 ANGLES ±1° FINISH		FEMALE HOUSING, 2 POSITION, 8.0mm CENTERLINE, 180 DEGREE, FAKRA	
		PRODUCT SPEC 108-32137 APPLICATION SPEC 114-32145		SIZE A1	
MATERIAL		WEIGHT		CAGE CODE -	
		CUSTOMER DRAWING		DRAWING NO. C=2203577	
		SCALE		SHEET	
		6:1		1 OF 2	
				REV	
				A1	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




DETAIL A
SCALE 4:1




DETAIL B
SCALE 4:1




DETAIL C
SCALE 4:1




DETAIL D
SCALE 4:1




DETAIL E
SCALE 4:1




DETAIL F
SCALE 4:1




DETAIL G
SCALE 4:1




DETAIL H
SCALE 4:1




DETAIL I
SCALE 4:1




DETAIL K
SCALE 4:1




DETAIL L
SCALE 4:1



DETAIL M
SCALE 4:1



DETAIL N
SCALE 4:1



DETAIL Z
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.005
1 PLC ±.005
2 PLC ±.005
3 PLC ±.005
4 PLC ±.005
ANGLES ±1°
FINISH -

MATERIAL

-

-

DWN J.A.BAKER 25APR2017
CHK E.R.LOVE 18JUL2017
APVD E.R.LOVE 18JUL2017

PRODUCT SPEC

108-32137

APPLICATION SPEC

114-32145

WEIGHT -

SIZE A1

CAGE CODE -

DRAWING NO. C=2203577

CUSTOMER DRAWING

NAME FEMALE HOUSING, 2 POSITION, 8.0mm CENTERLINE, 180 DEGREE, FAKRA

RESTRICTED TO -

SCALE 5:1

SHEET 2 OF 2

REV A1

TE Connectivity