




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ADDED NEW PNS -7 & -8	22JUL2024	SS	LET



VIEW A



NOTES:


- 1 PACKAGING: ACC. TO TE SPEC. 107-18064
- 2 ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857.
SHORT-CIRCUIT AND CONTINUITY TEST AT 500V DC, 0.1s
- 3 WIRING SCHEMA ACC. TO TIA/EIA-568-B AS SHOWN IN WIRING SCHEDULE
- 4 PROP 65 WARNING LABEL: SEE SHEET 2
- 5 LABEL TEXT:
TE CONNECTIVITY
WW/YY/PRODUCTION LOCATION CODE

WIRING SCHEDULE 3

CAVITY SIDE A	COLOR
1	WH/OG
2	OG
3	WH/GN
4	BU
5	WH/BU
6	GN
7	WH/BN
8	BN

4	20000 (±400)	HiFlex MultiPurpose 70°C PUR	2-2205130-8
	15000 (±300)	HiFlex MultiPurpose 70°C PUR	2-2205130-7
	10000 (±300)	HiFlex MultiPurpose 70°C PUR	2-2205130-6
	5000 (±150)	HiFlex MultiPurpose 70°C PUR	2-2205130-5
	3000 (±50)	HiFlex MultiPurpose 70°C PUR	2-2205130-4
	2000 (±25)	HiFlex MultiPurpose 70°C PUR	2-2205130-3
	1000 (±15)	HiFlex MultiPurpose 70°C PUR	2-2205130-2
	500 (±10)	HiFlex MultiPurpose 70°C PUR	2-2205130-1
OBSOLETE	10000 (±300)	HI 125°C TPE	1-2205130-6
	5000 (±150)	HI 125°C TPE	1-2205130-5
	3000 (±50)	HI 125°C TPE	1-2205130-4
	2000 (±25)	HI 125°C TPE	1-2205130-3
	1000 (±15)	HI 125°C TPE	1-2205130-2
	500 (±10)	HI 125°C TPE	1-2205130-1
	10000 (±300)	STD 110°C PVC	-2205130-6
	5000 (±150)	STD 110°C PVC	-2205130-5
	3000 (±50)	STD 110°C PVC	-2205130-4
	2000 (±25)	STD 110°C PVC	-2205130-3
	1000 (±15)	STD 110°C PVC	-2205130-2
	500 (±10)	STD 110°C PVC	-2205130-1
	Length "L"	Cable version	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.


DWN SATHISH KUMAR .G 03FEB2015	 TE Connectivity Ltd. CA MINI IO TYPE II PIGTAIL
CHK B.VELDHOVEN 03FEB2015	
APVD A.VAN ZANDVOORT 03FEB2015	
NAME	
PRODUCT SPEC 108-78955	RESTRICTED TO
APPLICATION SPEC 114-5506	SIZE A3
MATERIAL	CAGE CODE 00779
FINISH	DRAWING NO C-2205130
PRODUCT CHARACTERISTIC ACC. OMP EMEA_12 BESONDERE MERKMALE NACH OMP EMEA_12	SCALE NTS
	SHEET 1 of 2
	REV B1
CUSTOMER DRAWING	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



NOTES: CONTINUATION FROM SHEET 1:

4 PROP 65 WARNING LABEL:

- THE WARNING LABEL ON THE PRODUCT OR LOWEST LEVEL PACKAGING
- CHEMICAL NAME: ANTIMONY TRIOXIDE



WARNING: This product can expose you to chemicals including ANTIMONY TRIOXIDE which is known to the state of California to cause cancer. For more information, visit www.P65Warnings.ca.gov.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2015 SATHISH KUMAR .G	 TE Connectivity Ltd.				
		CHK 03FEB2015 B.VELDHOVEN					
DIMENSIONS: mm 		APVD 03FEB2015 A.VAN ZANDVOORT	NAME CA MINI IO TYPE II PIGTAIL				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC 108-78955					
MATERIAL -		FINISH -	APPLICATION SPEC 114-5506	SIZE A3	CAGE CODE 00779	DRAWING NO C-2205130	RESTRICTED TO -
CUSTOMER DRAWING			WEIGHT 0.000000	SCALE NTS	SHEET 2 OF 2	REV A4	