

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - by -

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
-	-	-	-	-	-		

NOTES:

Rated Current:3.0AMP

Contact Resistance:20mΩ Max.

Withstand Voltage:800V AC/DC

Insulation Resistance:1000MΩ Min.

Operation Temperature:-25°C to +85°C

Contact Material: Copper Alloy

Contact Plating: Gold Flash all over Nickel

Material: Polyester, UL94V-0 Black

Recommended P.C.B Layout

PART NUMBER AS SHOWN: 2271016-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ETHAN CHENG 29-NOV-13		
		CHK KOBBOY ZHAO 30-NOV-13		
DIMENSIONS: mm		APVD XU XIANG 30-NOV-13	NAME AMPMODU, PIN HEADER SHROUDED, THROUGH HOLE 2.50 PITCH, 2 POS	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-137777	RESTRICTED TO	
0 PLC ± -		APPLICATION SPEC	SIZE A2	CAGE CODE 00779
1 PLC ± -			DRAWING NO G= 2271016	
2 PLC ± ±0.25			SCALE 1:1	SHEET 1 of 1
3 PLC ± -				REV B
4 PLC ± -				
ANGLES ± -				
FINISH				
MATERIAL		WEIGHT -	CUSTOMER DRAWING	
SEE NOTES		SEE NOTES		

1471-9 (3/11)