

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL REL. PER LC20-0031-19	07MAY2019	JG	BJ
B		LC20-0082-20 / ECO-20-013130	16SEP2020	JG	BJ
C		NOTE 1 DELETED.	20DEC2021	RS	MP

FIGURE 1: 3/5 BC

FIGURE 2: 7/10/275 BC  
(No scale)

A  
(No scale)

Sliding ✓

Fixed ✓

(L)

M12 DIA STAINLESS STEEL BOLTS:44 LBF

MOUNTING HDW(IN)	IPS	øA	L	H	FIG.	DESCRIPTION	PART NUMBER	WEIGHT (Lbs)
1/2X1.0 5/8X1.25	2-1/2	2-7/8	11-5/16	3-1/8	1	5 TSD 82 P3-P5 T2*1/2IPS	2300995-1	6,1
1/2X1.0 5/8X1.25	3	3-1/2	11-5/16	3-5/8	1	5 TSD 82 P3-P5 T3*IPS	2300995-2	6,4
1/2X1.0 5/8X1.25	3-1/2	4	11-5/16	4	1	5 TSD 82 P3-P5 T3*1/2IPS	2300995-3	6,6
1/2X1.0 5/8X1.25	4	4-1/2	11-5/16	4-1/2	1	5 TSD 82 P3-P5 T4*IPS	2300995-4	7,2
1/2X1.0 5/8X1.25	5	5-9/16	11-5/16	5	1	5 TSD 82 P3-P5 T5*IPS	2300995-5	8,3
5/8X1.25 3/4X1.5	5	5-9/16	17-7/16	5	2	5 TSD 82 P7-P10-P275 T5*IPS	2300995-6	12,7
1/2X1.0 5/8X1.25	6	6-5/8	11-5/16	5-1/2	1	5 TSD 82 P3-P5 T6*IPS	2300995-7	8,8
5/8X1.25 3/4X1.5	6	6-5/8	17-7/16	5-1/2	2	5 TSD 82 P7-P10-P275 T6*IPS	2300995-8	13,1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M. PREVOT 23FEB2016

CHK A. BULZA

APVD B. JOHNSON

PRODUCT SPEC

APPLICATION SPEC

WEIGHT SEE TABLE

CUSTOMER DRAWING

TE Connectivity Ltd.

DOUBLE BOLTED BUS SUPPORT  
2 1/2 TO 6 INCH IPS  
SIMABUS

SIZE A3 CAGE CODE 00779 DRAWING NO C=2300995 RESTRICTED TO

SCALE NTS SHEET 1 OF 2 REV C

DIMENSIONS:

INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL

ALUM. ALLOY

FINISH

1470-19 (1/15)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - TE Connectivity Ltd.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

FIGURE 1: 76/127 BC

FIGURE 2: 178/225/275 BC

(No scale)

MOUNTING HDW<IN>	IPS	øA	L	H	FIG.	DESCRIPTION	PART NUMBER	WEIGHT (Lbs)
1/2X1.0 5/8X1.25	2-1/2	73.0	288	80	1	5 TSD 82 P3-P5 T2*1/2IPS	2300995-1	6,1
1/2X1.0 5/8X1.25	3	88.9	288	92	1	5 TSD 82 P3-P5 T3*IPS	2300995-2	6,4
1/2X1.0 5/8X1.25	3-1/2	101.6	288	102	1	5 TSD 82 P3-P5 T3*1/2IPS	2300995-3	6,6
1/2X1.0 5/8X1.25	4	114.3	288	112	1	5 TSD 82 P3-P5 T4*IPS	2300995-4	7,2
1/2X1.0 5/8X1.25	5	141.3	288	127	1	5 TSD 82 P3-P5 T5*IPS	2300995-5	8,3
5/8X1.25 3/4X1.5	5	141.3	443	127	2	5 TSD 82 P7-P10-P275 T5*IPS	2300995-6	12,7
1/2X1.0 5/8X1.25	6	168.3	288	140	1	5 TSD 82 P3-P5 T6*IPS	2300995-7	8,8
5/8X1.25 3/4X1.5	6	168.3	443	140	2	5 TSD 82 P7-P10-P275 T6*IPS	2300995-8	13,1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. PREVOT 23FEB2016	TE Connectivity Ltd.	
DIMENSIONS: mm		CHK A. BULZA		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B. JOHNSON	NAME DOUBLE BOLTED BUS SUPPORT 2 1/2 TO 6 INCH IPS SIMABUS	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC		
MATERIAL ALUM. ALLOY		FINISH	APPLICATION SPEC	RESTRICTED TO
		WEIGHT SEE TABLE	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=2300995	SCALE NTS
			SHEET 2 OF 2	REV C

1470-19 (1/15)