




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-22-153759	17JUL2023	MV	DZ

NOTES




1. GENERAL TOLERANCE : ±0.3
2. MATERIAL : PBT GRASS FILLED (UL94V-0)
3. MATING CONN. P/N
PLUG HOUSING : SEE TABLE
TAB CONTACT : 2232575-1




TYPE OF KEYING



SECT A-A



TYPE OF KEYING



3-2315883-4	TYPE D	YELLOW	3-2315884-4
2-2315883-3	TYPE C	BLUE	2-2315884-3
1-2315883-2	TYPE B	RED	1-2315884-2
2315883-1	TYPE A	NATURAL	2315884-1
MATING HSG P/N	TYPE OF KEYING	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH 仕上

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH 仕上

DWN K.SAKAI 31JAN2017

CHK DANIEL ZHANG 31JAN2017

APVD DANIEL ZHANG 31JAN2017

PRODUCT SPEC 製品規格 108-78350

APPLICATION SPEC 取付適用規格

WEIGHT 2.2 g

CUSTOMER DRAWING

TE Connectivity

2.5MM PITCH CONN W-W
WITH KEYING CAP HSG 8P

SIZE A3 CAGE CODE 00779 DRAWING NO. 2315884

RESTRICTED TO

SCALE 4:1 SHEET 1 OF 1 REV B